

RC-07P1N220000 - Contact insert



1594429

<https://www.phoenixcontact.com/us/products/1594429>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 7, contact connection type: Pin, Solder-in connection, series: RC, TU, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

The figure shows the 6-pos.
product version

Commercial data

Item number	1594429
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	ABRAFU
GTIN	4046356201308
Weight per piece (including packing)	11.31 g
Weight per piece (excluding packing)	8.74 g
Country of origin	DE

RC-07P1N220000 - Contact insert



1594429

<https://www.phoenixcontact.com/us/products/1594429>

Technical data

Product properties

Product type	Contact insert
Series	RC
	TU
Application	Signal
Number of positions	7
Connection profile	7
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Nominal current I_N	20 A (for max. connection cross section)
Nominal voltage U_N	48 V AC
	74 V DC
Degree of pollution	3
Rated surge voltage	2.5 kV

Connection data

Connection method	Solder-in connection
-------------------	----------------------

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

RC-07P1N220000 - Contact insert


1594429

<https://www.phoenixcontact.com/us/products/1594429>



Drawings

Drilling plan/solder pad geometry



RC-07P1N220000 - Contact insert



1594429

<https://www.phoenixcontact.com/us/products/1594429>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-07P1N220000 - Contact insert



1594429

<https://www.phoenixcontact.com/us/products/1594429>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	83510861-b0de-4499-bc6c-5b67c3ae3c46

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com