

# RC-07S1NC20000 - Contact insert



1594793

<https://www.phoenixcontact.com/us/products/1594793>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 6-pos.  
product version

Contact insert, M23, number of positions: 7, contact connection type: Socket, Solder-in connection, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1594793
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABRAFU
GTIN	4046356203456
Weight per piece (including packing)	10.67 g
Weight per piece (excluding packing)	6.9 g
Country of origin	DE

# RC-07S1NC20000 - Contact insert



1594793

<https://www.phoenixcontact.com/us/products/1594793>

## Technical data

### Product properties

Product type	Contact insert
Application	Signal
Number of positions	7
Connection profile	7
Coding	N
Thread type	M23

### Electrical properties

Contact: Contact group 1

Overvoltage category	III
Rated surge voltage	1.5 kV

### Connection data

Connection method	Solder-in connection
-------------------	----------------------

### Connector

Direction of rotation	Standard
-----------------------	----------

# RC-07S1NC20000 - Contact insert




1594793

<https://www.phoenixcontact.com/us/products/1594793>

## Drawings

Dimensional drawing




Dimensional drawing

# RC-07S1NC20000 - Contact insert

1594793

<https://www.phoenixcontact.com/us/products/1594793>

Schematic diagram



Connector pin assignment

# RC-07S1NC20000 - Contact insert



1594793

<https://www.phoenixcontact.com/us/products/1594793>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-07S1NC20000 - Contact insert



1594793

<https://www.phoenixcontact.com/us/products/1594793>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	92d06585-5cad-4a99-a2aa-88ff21c1920b

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)