

RC-Z2092 - Cable gland

1604245

<https://www.phoenixcontact.com/us/products/1604245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, external cable diameter 8 mm .. . 12 mm, shielding: no, connecting thread: Pg11, series: RC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1604245 |
| Packing unit | 20 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAFU |
| GTIN | 4046356248266 |
| Weight per piece (including packing) | 11.265 g |
| Weight per piece (excluding packing) | 8.34 g |
| Customs tariff number | 74198090 |
| Country of origin | DE |

RC-Z2092 - Cable gland



1604245

<https://www.phoenixcontact.com/us/products/1604245>

Technical data

Product properties

| | |
|--------------|-------------------|
| Product type | Cable screw gland |
| Series | RC |
| Shielded | no |

Dimensions

| | |
|-----------------------------|------|
| Thread type connection side | Pg11 |
|-----------------------------|------|

Material specifications

| | |
|-------------------------------|----------------------|
| Color | brass color |
| Material for screw connection | Brass, nickel-plated |

Cable/line

| | |
|-------------------------|----------------|
| External cable diameter | 8 mm ... 12 mm |
|-------------------------|----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

RC-Z2092 - Cable gland



1604245

<https://www.phoenixcontact.com/us/products/1604245>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140801 |
| ECLASS-15.0 | 27140801 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000441 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

RC-Z2092 - Cable gland



1604245

<https://www.phoenixcontact.com/us/products/1604245>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 40f322fe-03b8-4f08-a203-1bfb0770da0b |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com