

# RC-Z2202 - Cable gland

1604345

<https://www.phoenixcontact.com/us/products/1604345>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, external cable diameter 9 mm ..  
. 13 mm, shielding: no, connecting thread: Pg13,5, series: RC

## Commercial data

Item number	1604345
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356248891
Weight per piece (including packing)	32.125 g
Weight per piece (excluding packing)	30.64 g
Customs tariff number	74198090
Country of origin	DE

# RC-Z2202 - Cable gland



1604345

<https://www.phoenixcontact.com/us/products/1604345>

## Technical data

### Product properties

Product type	Cable screw gland
Series	RC
Shielded	no

### Dimensions

Wrench size, union nut	22 mm
Wrench size, support	22 mm
Thread type connection side	Pg13,5

### Material specifications

Color	brass color
Material for screw connection	Brass, nickel-plated

### Cable/line

External cable diameter	9 mm ... 13 mm
-------------------------	----------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP68
----------------------	------

# RC-Z2202 - Cable gland



1604345

<https://www.phoenixcontact.com/us/products/1604345>

## Classifications

### ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

### ETIM

ETIM 10.0	EC000441
-----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# RC-Z2202 - Cable gland



1604345

<https://www.phoenixcontact.com/us/products/1604345>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6ef36448-9300-4e81-9bce-36c3fb4cadbb

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)