

# RC-Z2462 - Cable clamp type cage and shield adapter



1604558

<https://www.phoenixcontact.com/us/products/1604558>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable clamp type cage and shield adapter, shielded: yes, cable diameter range: 2 mm ... 10.5 mm, series: NC, RC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1604558
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356249874
Weight per piece (including packing)	9.94 g
Weight per piece (excluding packing)	5.913 g
Customs tariff number	39269097
Country of origin	DE

# RC-Z2462 - Cable clamp type cage and shield adapter



1604558

<https://www.phoenixcontact.com/us/products/1604558>

## Technical data

### Product properties

Product type	Cable clamp type cage
Series	NC
	RC
Type of the screw connection	Universal with shield
Shielded	yes

### Cable/line

External cable diameter	2 mm ... 10.5 mm
-------------------------	------------------

### Mechanical properties

#### Mechanical data

Type of the screw connection	Universal with shield
------------------------------	-----------------------

# RC-Z2462 - Cable clamp type cage and shield adapter



1604558

<https://www.phoenixcontact.com/us/products/1604558>

## Classifications

### ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

### ETIM

ETIM 10.0	EC000441
-----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# RC-Z2462 - Cable clamp type cage and shield adapter



1604558

<https://www.phoenixcontact.com/us/products/1604558>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)