

# TU-0000000TUDU - Housing for circular connector



1605891

<https://www.phoenixcontact.com/us/products/1605891>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: TU, angled, Bayonet locking, M23, number of positions: 12, contact connection type: Socket, Crimp connection, shielded: yes, cable diameter range: 2 mm... 14.5 mm. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1605891
Packing unit	8 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAHE
GTIN	4046356255509
Weight per piece (including packing)	173.86 g
Weight per piece (excluding packing)	162.937 g
Customs tariff number	85389099
Country of origin	DE

# TU-0000000TUDU - Housing for circular connector



1605891

<https://www.phoenixcontact.com/us/products/1605891>

## Technical data

### Product properties

Product type	Circular connector housing
Series	TU
Application	Signal
Connection profile	12
Shielded	yes
Thread type	M23

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Material specifications

Material Housing	GD-Zn
Material Rotating parts	CuZn
Material Housing surface	Ni
Material Seal	FPM (O-ring)
Seal material	FPM or NBR or EPDM

### Connector

Type	angled
------	--------

### Cable/line

External cable diameter	2 mm ... 14.5 mm
-------------------------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

Drawings

Diagram



# TU-0000000TUDU - Housing for circular connector



1605891

<https://www.phoenixcontact.com/us/products/1605891>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# TU-0000000TUDU - Housing for circular connector



1605891

<https://www.phoenixcontact.com/us/products/1605891>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8ed9999c-4f49-4352-bc74-073bdcfb29e0

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)