

RC-06S1N320000 - Contact insert



1606994

<https://www.phoenixcontact.com/us/products/1606994>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 6, contact connection type: Socket, Solder-in connection, series: RC, TU

Commercial data

Item number	1606994
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356330251
Weight per piece (including packing)	13.11 g
Weight per piece (excluding packing)	5.62 g
Customs tariff number	85366990
Country of origin	DE

RC-06S1N320000 - Contact insert



1606994

<https://www.phoenixcontact.com/us/products/1606994>

Technical data

Product properties

Product type	Contact insert
Series	RC TU
Application	Signal
Number of positions	6
Connection profile	6
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Nominal current I_N	20 A (for max. connection cross section)
Nominal voltage U_N	300 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	2.5 kV

Connection data

Connection method	Solder-in connection
-------------------	----------------------

Material specifications

Material Insulating body	PBT
Material Contact	CuZn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

RC-06S1N320000 - Contact insert


1606994

<https://www.phoenixcontact.com/us/products/1606994>



Drawings

Dimensional drawing



Dimensional drawing

RC-06S1N320000 - Contact insert

1606994

<https://www.phoenixcontact.com/us/products/1606994>



Schematic diagram



Connector pin assignment


RC-06S1N320000 - Contact insert



1606994

<https://www.phoenixcontact.com/us/products/1606994>

Drilling plan/solder pad geometry



RC-06S1N320000 - Contact insert



1606994

<https://www.phoenixcontact.com/us/products/1606994>

Classifications

ECLASS

ECLASS-13.0	27440223
-------------	----------

RC-06S1N320000 - Contact insert



1606994

<https://www.phoenixcontact.com/us/products/1606994>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com