

# RM-00000007100 - Housing for circular connector



1607027

<https://www.phoenixcontact.com/us/products/1607027>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RM, straight, Screw locking mechanism, M23, shielded: no. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1554106

## Commercial data

Item number	1607027
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFI
GTIN	4046356278508
Weight per piece (including packing)	75.23 g
Weight per piece (excluding packing)	71.84 g
Customs tariff number	85366990
Country of origin	DE

# RM-00000007100 - Housing for circular connector



1607027

<https://www.phoenixcontact.com/us/products/1607027>

## Technical data

### Product properties

Product type	Circular connector housing
Series	RM
Application	Signal
Shielded	no
Thread type	M23

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Rotating parts	CuZn
Material Seal	FPM

### Connector

Type	straight
------	----------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# RM-00000007100 - Housing for circular connector



1607027

<https://www.phoenixcontact.com/us/products/1607027>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

1607027

<https://www.phoenixcontact.com/us/products/1607027>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d490e7dd-c03c-4728-b410-15f4dc256224

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)