

RC-09S1N320000 - Contact insert



1607003

<https://www.phoenixcontact.com/us/products/1607003>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 8+1, contact connection type: Socket, Solder-in connection, series: RC, TU

The figure shows the 6-pos. product version

Commercial data

Item number	1607003
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356210485
Weight per piece (including packing)	4.94 g
Weight per piece (excluding packing)	4.94 g
Customs tariff number	85389099
Country of origin	DE

RC-09S1N320000 - Contact insert



1607003

<https://www.phoenixcontact.com/us/products/1607003>

Technical data

Product properties

Product type	Contact insert
Series	RC TU
Application	Signal
Number of positions	9
Connection profile	8+1
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Nominal current I_N	20 A
Nominal voltage U_N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	48 V AC 74 V DC

Connection data

Connection method	Solder-in connection
-------------------	----------------------

Material specifications

Material Insulating body	PBT
Material Contact	Cu/Zn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----


RC-09S1N320000 - Contact insert

1607003

<https://www.phoenixcontact.com/us/products/1607003>



Drawings




RC-09S1N320000 - Contact insert

1607003


<https://www.phoenixcontact.com/us/products/1607003>



Schematic diagram



Drilling plan/solder pad geometry



RC-09S1N320000 - Contact insert



1607003

<https://www.phoenixcontact.com/us/products/1607003>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com