

SC-5EP1N8AWV00 - Device connector front mounting



1615543

<https://www.phoenixcontact.com/us/products/1615543>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Schematic view

Device connector front mounting, application: Power, straight, Screw locking mechanism, M23, number of positions: 5+PE, contact connection type: Pin, Axial O-ring, 4x Ø 3.2, flange dimensions: 26 mm x 26 mm, connection method: Crimp connection, series: SC

Commercial data

Item number	1615543
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRIFA
GTIN	4046356542739
Weight per piece (including packing)	33.98 g
Weight per piece (excluding packing)	25.3 g
Country of origin	DE

1615543

<https://www.phoenixcontact.com/us/products/1615543>

Technical data

Notes

Order information:	Order crimp contacts 6 x Ø 2 mm separately
--------------------	--

Product properties

Product type	Circular connectors (device side)
Series	SC
Application	Power
Connection profile	5+PE
Coding	N
Thread type	M23

Dimensions

Housing

Flange dimensions	26 mm x 26 mm
-------------------	---------------

Material specifications

Housing material	Stainless steel
------------------	-----------------

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
------------------	------

Contact: Contact group 2

Contact diameter	2 mm
------------------	------

Connection data

Conductor connection

Connection method	Crimp connection
Contact connection type	Pin

Connector

Type	straight
------	----------

Environmental and real-life conditions

Ambient conditions

Altitude	3000 m
----------	--------

SC-5EP1N8AWV00 - Device connector front mounting



1615543

<https://www.phoenixcontact.com/us/products/1615543>

Classifications

UNSPSC

UNSPSC 21.0	39121419
-------------	----------

SC-5EP1N8AWV00 - Device connector front mounting



1615543

<https://www.phoenixcontact.com/us/products/1615543>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com