

UC-07S1NS2F3DU - Coupler connector



1618481

<https://www.phoenixcontact.com/us/products/1618481>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Coupler connector, application: Signal, series: UC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Socket, Screw connection, cable diameter range: 2 mm ... 14.5 mm, coding: N

Commercial data

Item number	1618481
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIG
GTIN	4046356619622
Weight per piece (including packing)	118.42 g
Weight per piece (excluding packing)	118.42 g
Country of origin	DE

UC-07S1NS2F3DU - Coupler connector



1618481

<https://www.phoenixcontact.com/us/products/1618481>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Insertion/withdrawal cycles	50
Connection method	Screw connection
Contact switching type	Socket
Application	Signal
Number of positions	7
Direction of rotation	Standard
Connection profile	7
Number (Contact group 1)	7
Contact diameter (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Order information:	Order contact inserts separately
Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	Pg13,5
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

UC-07S1NS2F3DU - Coupler connector

1618481

<https://www.phoenixcontact.com/us/products/1618481>

Drawings

Schematic diagram



Connector pin assignment


UC-07S1NS2F3DU - Coupler connector



1618481

<https://www.phoenixcontact.com/us/products/1618481>

Schematic diagram




UC-07S1NS2F3DU - Coupler connector



1618481

<https://www.phoenixcontact.com/us/products/1618481>



Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com