

RF-17P1N8AWA00S - Device connector front mounting



1619560

<https://www.phoenixcontact.com/us/products/1619560>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version

Device connector front mounting, application: Feedback, signal, straight, SPEEDCON, M23, number of positions: 17, contact connection type: Pin, Axial O-ring, 4x Ø 3.2, shielded: yes, number of positions: 17, connection method: Crimp connection, series: RF

Commercial data

Item number	1619560
Packing unit	40 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAGL
GTIN	4046356630450
Weight per piece (including packing)	107.5 g
Weight per piece (excluding packing)	107.5 g
Country of origin	DE

RF-17P1N8AWA00S - Device connector front mounting



1619560

<https://www.phoenixcontact.com/us/products/1619560>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connectors (device side)
Series	RF
Application	Feedback, signal Signal
Number of positions	17
Connection profile	17
Shielded	yes
Coding	N
Thread type	M23

Material specifications

Seal material	FPM
---------------	-----

Electrical properties

Contact

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Crimp connection
Contact connection type	Pin

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C

RF-17P1N8AWA00S - Device connector front mounting



1619560

<https://www.phoenixcontact.com/us/products/1619560>

Altitude	2000 m
----------	--------

RF-17P1N8AWA00S - Device connector front mounting




1619560

<https://www.phoenixcontact.com/us/products/1619560>

Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), standard pin

RF-17P1N8AWA00S - Device connector front mounting



1619560

<https://www.phoenixcontact.com/us/products/1619560>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RF-17P1N8AWA00S - Device connector front mounting



1619560

<https://www.phoenixcontact.com/us/products/1619560>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com