

# CA-00000002S00 - Housing for circular connector



1620541

<https://www.phoenixcontact.com/us/products/1620541>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector, front mounting without contact insert, straight, SPEEDCON locking, M23, flat gasket, 4x Ø 3.2, shielded: yes, flange dimensions: 25 mm x 25 mm

## Commercial data

Item number	1620541
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEP
GTIN	4046356828857
Weight per piece (including packing)	22 g
Weight per piece (excluding packing)	17.479 g
Customs tariff number	85366990
Country of origin	DE

1620541

<https://www.phoenixcontact.com/us/products/1620541>

## Technical data

### Product properties

Product type	Circular connector housing
Series	CA
Application	Signal
Shielded	yes
Thread type	M23

### Dimensions

#### Housing

Flange dimensions	25 mm x 25 mm
-------------------	---------------

### Material specifications

Material Housing	GD-Zn
------------------	-------

### Connector

Type	straight
------	----------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
Altitude	2000 m

### Mounting

Mounting type	Front mounting/square flange (4x Ø 3.2 mm)
---------------	--

# CA-00000002S00 - Housing for circular connector



1620541

<https://www.phoenixcontact.com/us/products/1620541>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# CA-00000002S00 - Housing for circular connector



1620541

<https://www.phoenixcontact.com/us/products/1620541>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)