

# CA-0000000AD00 - Housing for circular connector



1621737

<https://www.phoenixcontact.com/us/products/1621737>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: CA, angled rotatable, for standard and SPEEDCON interlock, M23, Axial O-ring, shielded: yes. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1621737
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAEQ
GTIN	4055626000541
Weight per piece (including packing)	116.866 g
Weight per piece (excluding packing)	110.258 g
Country of origin	DE

# CA-0000000AD00 - Housing for circular connector



1621737

<https://www.phoenixcontact.com/us/products/1621737>

## Technical data

### Product properties

Product type	Circular connector housing
Series	CA
Application	Signal
Shielded	yes
Thread type	M23

### Material specifications

Material Housing	GD-Zn
Material Rotating parts	CuZn

### Connector

Type	angled rotatable
------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
Altitude	2000 m

### Mounting

Mounting type	Front mounting/square flange (4x Ø 3.2 mm)
---------------	--

# CA-0000000AD00 - Housing for circular connector



1621737

<https://www.phoenixcontact.com/us/products/1621737>

## Classifications

### ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

### ETIM

ETIM 10.0	EC003556
-----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# CA-0000000AD00 - Housing for circular connector



1621737

<https://www.phoenixcontact.com/us/products/1621737>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)