

HC-26P1N8AWF00J - Device connector front mounting



1623259

<https://www.phoenixcontact.com/us/products/1623259>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, application: Signal, straight, Screw locking mechanism, number of positions: 26, Axial O-ring, shielded: yes, flange dimensions: 30 mm x 30 mm, number of positions: 26, series: HC

Commercial data

Item number	1623259
Packing unit	70 pc
Minimum order quantity	70 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJL
GTIN	4055626273167
Weight per piece (including packing)	41.23 g
Weight per piece (excluding packing)	38.902 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Mounting

Mounting type	Front mounting/square flange (4x Ø 3.2 mm)
---------------	--

Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Pg screw connection	none

Dimensions

Housing

Flange dimensions	30 mm x 30 mm
-------------------	---------------

Material specifications

Material Housing	Metal
Flammability rating according to UL 94	V0
Seal material	FPM or NBR or EPDM

Electrical properties

Contact

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions

HC-26P1N8AWF00J - Device connector front mounting




1623259

<https://www.phoenixcontact.com/us/products/1623259>

Degree of protection	IP67, when plugged in
----------------------	-----------------------

Drawings

Schematic diagram



Connector pin assignment

HC-26P1N8AWF00J - Device connector front mounting



1623259

<https://www.phoenixcontact.com/us/products/1623259>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 10.0	EC003569
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1623259

<https://www.phoenixcontact.com/us/products/1623259>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9ce97f20-5ba1-4d5f-918e-23c5ec2a86a6

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com