

# HC-26P1N8AWA00 - Device connector front mounting



1623268

<https://www.phoenixcontact.com/us/products/1623268>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, Radial O-ring, 4x Ø 3.2, shielded: yes, flange dimensions: 30 mm x 30 mm, number of positions: 26, connection method: Crimp connection, series: HC

## Commercial data

Item number	1623268
Packing unit	24 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAJL
GTIN	4055626272917
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

### Dimensions

#### Housing

Flange dimensions	30 mm x 30 mm
-------------------	---------------

### Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal

### Electrical properties

#### Contact

Contact diameter	1 mm
Nominal current $I_N$	8 A
Nominal voltage $U_N$	150 V
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connection data

#### Conductor connection

Connection method	Crimp connection
Contact connection type	Pin

### Connector

Type	straight
Direction of rotation	Standard

### Environmental and real-life conditions

# HC-26P1N8AWA00 - Device connector front mounting



1623268

<https://www.phoenixcontact.com/us/products/1623268>

## Ambient conditions

Degree of protection	IP67, when plugged in
----------------------	-----------------------

# HC-26P1N8AWA00 - Device connector front mounting




1623268

<https://www.phoenixcontact.com/us/products/1623268>


## Drawings

Dimensional drawing



## Installation dimensions


Dimensional drawing



1623268

<https://www.phoenixcontact.com/us/products/1623268>

Schematic diagram



Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)