

SACC-M12MS-4QO-0,75M TURCK - Connector



1642234

<https://www.phoenixcontact.com/us/products/1642234>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, 4-position, Plug straight M12, coding: A, knurl material: Zinc die-cast, nickel-plated, Customer version

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1642234 |
| Packing unit | 50 pc |
| Minimum order quantity | 1 pc |
| Product key | AF2CCA |
| GTIN | 4017918936501 |
| Weight per piece (including packing) | 18.478 g |
| Weight per piece (excluding packing) | 18.478 g |
| Country of origin | DE |

SACC-M12MS-4QO-0,75M TURCK - Connector



1642234

<https://www.phoenixcontact.com/us/products/1642234>

Technical data

Product properties

| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Coding | A |
| Cable outlet | straight |

Dimensions

External dimensions

| | |
|------------------|----------|
| Outside diameter | 7.5 4 mm |
|------------------|----------|

Material specifications

| | |
|-------------------------------|------------------------------|
| Material for screw connection | Zinc die-cast, nickel-plated |
|-------------------------------|------------------------------|

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Plug |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | A |

SACC-M12MS-4QO-0,75M TURCK - Connector



1642234

<https://www.phoenixcontact.com/us/products/1642234>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

SACC-M12MS-4QO-0,75M TURCK - Connector



1642234

<https://www.phoenixcontact.com/us/products/1642234>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com