

HC-D 7-SD-FL/FS-MD - Protective cover



1644300

<https://www.phoenixcontact.com/us/products/1644300>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover D7, for single locking latch, protective cover material: PA, height: 17 mm, seal: yes, with lanyard

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1644300 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF66 |
| Product key | AF7AZC |
| GTIN | 4017918896867 |
| Weight per piece (including packing) | 10.82 g |
| Weight per piece (excluding packing) | 8 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

HC-D 7-SD-FL/FS-MD - Protective cover

1644300


<https://www.phoenixcontact.com/us/products/1644300>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Protective cover |
| Housing type | Protective cover |
| Type | D7 |
| Seal present | yes |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 26.5 mm |
| Height | 17 mm |
| Length | 26.5 mm |
| Diameter | 30 mm |

Material specifications

| | |
|--|-----|
| Flammability rating according to UL 94 | V2 |
| Seal material | NBR |
| Material, protective cover | PA |

Mechanical properties

Mechanical data

| | |
|--------------|-----|
| Locking type | Pin |
|--------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP54 |
| Ambient temperature (operation) | -20 °C ... 100 °C |

Mounting

| | |
|---------------|--|
| Assembly note | Plastic protective cover for short-term protection |
|---------------|--|

HC-D 7-SD-FL/FS-MD - Protective cover




1644300

<https://www.phoenixcontact.com/us/products/1644300>

Drawings

Dimensional drawing



Dimensional drawing

HC-D 7-SD-FL/FS-MD - Protective cover



1644300

<https://www.phoenixcontact.com/us/products/1644300>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440208 |
| ECLASS-15.0 | 27440208 |

HC-D 7-SD-FL/FS-MD - Protective cover



1644300

<https://www.phoenixcontact.com/us/products/1644300>

Environmental product compliance

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com