

HC-B 24-SMLD-84/O1M32 - Housing



1645781

<https://www.phoenixcontact.com/us/products/1645781>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON box mounting base B24, with single locking latch, height 84 mm, with supports 1x M32 with cover

Commercial data

Item number	1645781
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	AF7AAC
GTIN	4017918956868
Weight per piece (including packing)	540.83 g
Weight per piece (excluding packing)	540.83 g
Country of origin	DE

HC-B 24-SMLD-84/O1M32 - Housing

1645781


<https://www.phoenixcontact.com/us/products/1645781>

Technical data

Product properties

Product type	Housing with locking latch
Housing type	Surface mounting housing
Application	Standard
Type	B24
No. of cable outlets	1
Type of the screw connection	1x M32
Protective cover	yes
Shielded	no
Cable outlet	left (view of the opened single locking latch)
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57 mm
Height	84 mm
Length	144 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Material, protective cover	PA
Locking latch material	Stainless steel, handle: PA

Mechanical properties

Mechanical data

Type of the screw connection	1x M32
Locking type	Latch

Mounting

Assembly note	For half and full screw connections
---------------	-------------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (When plugged in)
	IP54 (with closed protective cover)

HC-B 24-SMLD-84/O1M32 - Housing



1645781

<https://www.phoenixcontact.com/us/products/1645781>

Ambient temperature (operation)

-40 °C ... 125 °C

HC-B 24-SMLD-84/O1M32 - Housing




1645781

<https://www.phoenixcontact.com/us/products/1645781>

Drawings

Dimensional drawing



Dimensional drawing; $h = 84$ mm

HC-B 24-SMLD-84/O1M32 - Housing



1645781

<https://www.phoenixcontact.com/us/products/1645781>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

HC-B 24-SMLD-84/O1M32 - Housing



1645781

<https://www.phoenixcontact.com/us/products/1645781>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com