

# HC-M-BS-M16 - Screw plug

1646227

<https://www.phoenixcontact.com/us/products/1646227>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Filler plug, metal, size: M16



## Commercial data

Item number	1646227
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4017918927981
Weight per piece (including packing)	7.4 g
Weight per piece (excluding packing)	7 g
Customs tariff number	74198090
Country of origin	DE

# HC-M-BS-M16 - Screw plug

1646227

<https://www.phoenixcontact.com/us/products/1646227>

## Technical data

### Product properties

Product type	Plug for cable screw gland
--------------	----------------------------


### Connection data

Tightening torque	3.5 Nm
-------------------	--------

### Ex data

Suited for EX-applications	no
----------------------------	----

### Dimensions

Dimensional drawing	
Length	8 mm
Length of the connecting thread	5 mm
Length without connecting thread	3 mm
Diameter Connecting thread	16 mm
Connecting thread diameter	16 mm
Wrench size, union nut	18 mm
Hexagon angular dimension	20 mm
Thread type connection side	M16 x 1.5
Thread pitch	1.5 mm

### Material specifications

Material	Brass, nickel-plated
Seal material O-ring	NBR
Housing surface material	Ni
Material for screw connection	Brass, nickel-plated

### Cable/line

Halogen-free	no
--------------	----

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

# HC-M-BS-M16 - Screw plug


1646227

<https://www.phoenixcontact.com/us/products/1646227>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-M-BS-M16 - Screw plug



1646227

<https://www.phoenixcontact.com/us/products/1646227>

## Classifications

### ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	27140805

### ETIM

ETIM 10.0	EC000032
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-M-BS-M16 - Screw plug



1646227

<https://www.phoenixcontact.com/us/products/1646227>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f799b032-6e08-4e2a-986d-0061bc60a1f1

### EF3.1 Climate Change

CO2e kg	0.136 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)