

VS-08-A-S-RJ45/MOD-1-IP67 - Panel-mount frame



1652868

<https://www.phoenixcontact.com/us/products/1652868>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame, IP67, irradiated for welding applications, for modular socket inserts (Keystone), for square panel cutout, with grommet, without mounting screws

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1652868 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | ABNMAY |
| GTIN | 4017918969882 |
| Weight per piece (including packing) | 5.7 g |
| Weight per piece (excluding packing) | 5.6 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

VS-08-A-S-RJ45/MOD-1-IP67 - Panel-mount frame



1652868

<https://www.phoenixcontact.com/us/products/1652868>

Technical data


Product properties

| | |
|--------------|-----------------------|
| Product type | Panel-mount frame |
| Type | RJ45, IP67, version 6 |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 32.5 mm |
| Height | 32.5 mm |
| Depth | 16 mm |

Material specifications

| | |
|--|-------|
| Color | black |
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Housing material | PA |

Mechanical properties

Mechanical data

| | |
|-----------------------------|--------|
| Insertion/withdrawal cycles | ≥ 1000 |
|-----------------------------|--------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 80 °C |

VS-08-A-S-RJ45/MOD-1-IP67 - Panel-mount frame




1652868

<https://www.phoenixcontact.com/us/products/1652868>


Drawings

Dimensional drawing



RJ45 panel mounting frame, IP67

Dimensional drawing



Mounting cutout

VS-08-A-S-RJ45/MOD-1-IP67 - Panel-mount frame



1652868

<https://www.phoenixcontact.com/us/products/1652868>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com