

# VS-TO-IW-2-F-9010 - Terminal outlet



1653016

<https://www.phoenixcontact.com/us/products/1653016>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal outlet, flush-type mounting, IP20, two slots for contact inserts with the Freenet system



## Commercial data

Item number	1653016
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB15
Product key	ABNGCB
GTIN	4017918962081
Weight per piece (including packing)	48.6 g
Weight per piece (excluding packing)	48.6 g
Customs tariff number	85366990
Country of origin	DE

# VS-TO-IW-2-F-9010 - Terminal outlet

1653016


<https://www.phoenixcontact.com/us/products/1653016>

## Technical data

### Product properties

Product type	Network distributor box
Application	Einbauplätze für Kontakteinsätze mit Freenet-System
No. of cable outlets	2
Number of slots	2

### Dimensions

Dimensional drawing	
Width	80 mm
Length	80 mm

### Material specifications

Color	pure white RAL 9010
Flammability rating according to UL 94	HB
Housing material	PC+ABS

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	5 °C ... 55 °C

### Mounting

Mounting type	UP/channel installation
---------------	-------------------------

# VS-TO-IW-2-F-9010 - Terminal outlet




1653016

<https://www.phoenixcontact.com/us/products/1653016>

## Drawings

Dimensional drawing



Terminal outlet

# VS-TO-IW-2-F-9010 - Terminal outlet



1653016

<https://www.phoenixcontact.com/us/products/1653016>

## Classifications

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# VS-TO-IW-2-F-9010 - Terminal outlet



1653016

<https://www.phoenixcontact.com/us/products/1653016>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)