


# VS-04-BUB-FK-F/IP67 - USB female insert



1653867

<https://www.phoenixcontact.com/us/products/1653867>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB socket insert, 4-pos., socket USB type B on flat-ribbon cable terminal strip, pitch 2.54, for the Freenet system in the panel mounting frame, IP20 terminal outlet, 19" patch panel and service interface

## Commercial data

Item number	1653867
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNNFC
GTIN	4017918970192
Weight per piece (including packing)	14.4 g
Weight per piece (excluding packing)	7.05 g
Customs tariff number	85366990
Country of origin	DE

1653867

<https://www.phoenixcontact.com/us/products/1653867>

## Technical data

### Product properties

Product type	Female insert
Type	USB-A
Number of positions	4
Connection profile	USB
Number of slots	1
Shielded	no

### Electrical properties

Rated voltage (III/3)	30 V
Rated current	1 A
Insulation resistance	≥ 1 GΩ
Transmission medium	Copper
Transmission characteristics (category)	USB 2.0

### Connection data

#### Connection technology

Connection method	Flat-ribbon cable connection
-------------------	------------------------------

### Dimensions

Width	22.8 mm
Height	17.7 mm
Length	36.1 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	Thermoplastic

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-15 °C ... 65 °C

# VS-04-BUB-FK-F/IP67 - USB female insert


1653867

<https://www.phoenixcontact.com/us/products/1653867>

## Drawings

Schematic diagram

Pin	USB B
1	GND
2	
3	Shield
4	
5	D+
6	D-
7	Shield
8	
9	VBUS
10	




Contact assignment

# VS-04-BUB-FK-F/IP67 - USB female insert

1653867

<https://www.phoenixcontact.com/us/products/1653867>

Schematic diagram



Pin assignment socket USB, type B

# VS-04-BUB-FK-F/IP67 - USB female insert



1653867

<https://www.phoenixcontact.com/us/products/1653867>

## Classifications

### ECLASS

ECLASS-15.0	27440318
ECLASS-13.0	27440390

### ETIM

ETIM 10.0	EC004746
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-04-BUB-FK-F/IP67 - USB female insert



1653867

<https://www.phoenixcontact.com/us/products/1653867>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)