

VS-SCRJ-PC - Protective cover



1653757

<https://www.phoenixcontact.com/us/products/1653757>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP67 protective cover, for covering the male inserts in the sleeve housings IP67, VS-SC-RJ-..., VS-04-..., VS-06-... and VS-08-...



Commercial data

Item number	1653757
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AB17
Product key	ABNNBZ
GTIN	4017918970130
Weight per piece (including packing)	4.02 g
Weight per piece (excluding packing)	3.29 g
Customs tariff number	39269097
Country of origin	CH

VS-SCRJ-PC - Protective cover



1653757

<https://www.phoenixcontact.com/us/products/1653757>

Technical data

Product properties

Product type	Protective cover
Type	SCRJ
Connection profile	SCRJ

Electrical properties

Transmission medium	FO
---------------------	----

Dimensions

Width	30 mm
Height	21 mm
Length	40.5 mm

Material specifications

Color	gray
Material	Plastic
Flammability rating according to UL 94	V0
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C

VS-SCRJ-PC - Protective cover



1653757

<https://www.phoenixcontact.com/us/products/1653757>

Classifications

ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

ETIM

ETIM 10.0	EC002314
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-SCRJ-PC - Protective cover



1653757

<https://www.phoenixcontact.com/us/products/1653757>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.264 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com