

VS-04-BUA-BUB-F/IP67 - USB female insert

1653838

<https://www.phoenixcontact.com/us/products/1653838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB socket insert, 4-pos., socket USB type A on socket USB type B, for the Freenet system in the panel mounting frame, IP20 terminal outlet, 19" patch panel and service interface, pluggable from both directions

Commercial data

Item number	1653838
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABNDAS
GTIN	4017918970161
Weight per piece (including packing)	17.1 g
Weight per piece (excluding packing)	16.5 g
Customs tariff number	85366990
Country of origin	DE

VS-04-BUA-BUB-F/IP67 - USB female insert



1653838

<https://www.phoenixcontact.com/us/products/1653838>

Technical data

Product properties

Product type	Female insert
Number of positions	4
Connection profile	USB

Electrical properties

Rated voltage (III/3)	30 V
Rated current	1 A
Insulation resistance	≥ 1 GΩ
Transmission characteristics (category)	USB 2.0

Connection data

Connection technology

Connection method	Socket, type B
-------------------	----------------

Material specifications

Flammability rating according to UL 94	V0
Housing material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	Thermoplastic

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-15 °C ... 65 °C


VS-04-BUA-BUB-F/IP67 - USB female insert

1653838

<https://www.phoenixcontact.com/us/products/1653838>


Drawings

Schematic diagram



Pin assignment socket USB, type A

Schematic diagram



Pin assignment socket USB, type B

VS-04-BUA-BUB-F/IP67 - USB female insert



1653838

<https://www.phoenixcontact.com/us/products/1653838>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com