

VS-08-BU-RJ45-3/BU - RJ45 coupling



1654552

<https://www.phoenixcontact.com/us/products/1654552>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

RJ45 socket insert, modular (Keystone), CAT3, 8-pos., shielded, socket on socket



Commercial data

Item number	1654552
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNACB
GTIN	4017918955076
Weight per piece (including packing)	9.1 g
Weight per piece (excluding packing)	8.99 g
Customs tariff number	85366990
Country of origin	TW

1654552

<https://www.phoenixcontact.com/us/products/1654552>

Technical data

Product properties

Product type	Female insert
Type	RJ45
Number of positions	8
Connection profile	RJ45
Number of slots	1
Shielded	yes

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Rated voltage (III/3)	72 V (DC)
Insulation resistance	≥ 500 MΩ
Transmission medium	Copper
Transmission characteristics (category)	CAT3

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Interfaces

Signal type/category	Ethernet
----------------------	----------

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold

Cable/line

Signal type/category	Ethernet
----------------------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

VS-08-BU-RJ45-3/BU - RJ45 coupling



1654552

<https://www.phoenixcontact.com/us/products/1654552>

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440390

ETIM

ETIM 9.0	EC004746
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-08-BU-RJ45-3/BU - RJ45 coupling



1654552

<https://www.phoenixcontact.com/us/products/1654552>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com