

HC-D 15-ADP/1 DSUB 25 (VE 250) - Adapter plate



1660740

<https://www.phoenixcontact.com/us/products/1660740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB adapter plate, for one D-SUB connector, no. of positions 25, housing series HC-D 15...

Product description

Adapter plate, incl. mounting screws

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1660740 |
| Packing unit | 250 pc |
| Minimum order quantity | 1 pc |
| Product key | AF7AZD |
| GTIN | 4017918256647 |
| Weight per piece (including packing) | 7.9 g |
| Weight per piece (excluding packing) | 7.9 g |
| Country of origin | DE |

HC-D 15-ADP/1 DSUB 25 (VE 250) - Adapter plate



1660740


<https://www.phoenixcontact.com/us/products/1660740>

Technical data

Product properties

| | |
|---------------------|---------------|
| Product type | Adapter plate |
| Type | D15 |
| Number of positions | 25 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 23 mm |
| Height | 7 mm |
| Length | 57 mm |

Material specifications

| | |
|--|------|
| Color | gray |
| Material | PA |
| Flammability rating according to UL 94 | HB |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -20 °C ... 100 °C |
|---------------------------------|-------------------|

Mounting

| | |
|---------------|---|
| Assembly note | <p>With mounting screws: 1) Phillips self-tapping screw 2.9 x 6.2/2) M3 x 10 DIN 84</p> <p>Mounting position of the adapter plate in the sleeve housing: T is visible after mounting in the housing. Mounting position of the adapter plate in the panel mounting base/socket housing/coupling housing: A is visible after mounting in the housing. Mounting position of the D-SUB (after mounting in the housing): in front of the mounting panel (front mounting)</p> |
|---------------|---|

HC-D 15-ADP/1 DSUB 25 (VE 250) - Adapter plate




1660740

<https://www.phoenixcontact.com/us/products/1660740>

Drawings

Dimensional drawing



See assembly instruction

HC-D 15-ADP/1 DSUB 25 (VE 250) - Adapter plate



1660740

<https://www.phoenixcontact.com/us/products/1660740>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440201 |
| ECLASS-15.0 | 27440201 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121421 |
|-------------|----------|

HC-D 15-ADP/1 DSUB 25 (VE 250) - Adapter plate



1660740

<https://www.phoenixcontact.com/us/products/1660740>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com