

# HC-BS-PG16 - Screw plug

1674516

<https://www.phoenixcontact.com/us/products/1674516>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw plug, material for screw connection: Brass, nickel-plated, connecting thread: Pg16, color: silver-colored



## Commercial data

Item number	1674516
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4017918135416
Weight per piece (including packing)	17.41 g
Weight per piece (excluding packing)	16.96 g
Customs tariff number	74198090
Country of origin	DE

# HC-BS-PG16 - Screw plug

1674516

<https://www.phoenixcontact.com/us/products/1674516>



## Technical data

### Product properties

Product type	Plug for cable screw gland
Pg screw connection	Pg16

### Dimensions

Dimensional drawing	
Length	10 mm
Length of the connecting thread	6 mm
Diameter	26 mm
Hexagon angular dimension	Diameter (no corners)
Thread type connection side	Pg16

### Material specifications

Material	Brass, nickel-plated
Seal material O-ring	NBR
Housing surface material	Ni
Material for screw connection	Brass, nickel-plated

### Cable/line

Halogen-free	no
--------------	----

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

# HC-BS-PG16 - Screw plug


1674516

<https://www.phoenixcontact.com/us/products/1674516>



## Drawings

Dimensional drawing



Filler plugs Pg16

# HC-BS-PG16 - Screw plug

1674516

<https://www.phoenixcontact.com/us/products/1674516>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674516>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-BS-PG16 - Screw plug

1674516

<https://www.phoenixcontact.com/us/products/1674516>



## Classifications

### ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	27140805

### ETIM

ETIM 10.0	EC000032
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-BS-PG16 - Screw plug



1674516

<https://www.phoenixcontact.com/us/products/1674516>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cb962708-6dc7-46f6-9b04-36c8f08f0b36

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)