

# HC-BS-PG36 - Screw plug

1674545

<https://www.phoenixcontact.com/us/products/1674545>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw plug, connecting thread: Pg36, color: silver-colored



## Commercial data

Item number	1674545
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4017918135447
Weight per piece (including packing)	72.1 g
Weight per piece (excluding packing)	65.87 g
Customs tariff number	74198090
Country of origin	DE

# HC-BS-PG36 - Screw plug

1674545

<https://www.phoenixcontact.com/us/products/1674545>

## Technical data

### Product properties

Product type	Plug for cable screw gland
Pg screw connection	Pg36

### Dimensions

Dimensional drawing	
Length	13 mm
Length of the connecting thread	8 mm
Diameter	50 mm 50 mm
Hexagon angular dimension	Diameter (no corners)
Thread type connection side	Pg36

### Material specifications

Color	brass color
Material	Brass, nickel-plated
Seal material O-ring	NBR
Housing surface material	Ni

### Cable/line

Halogen-free	no
--------------	----

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

# HC-BS-PG36 - Screw plug


1674545

<https://www.phoenixcontact.com/us/products/1674545>



## Drawings

Dimensional drawing



Filler plugs Pg36

# HC-BS-PG36 - Screw plug

1674545

<https://www.phoenixcontact.com/us/products/1674545>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674545>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-BS-PG36 - Screw plug



1674545

<https://www.phoenixcontact.com/us/products/1674545>

## Classifications

### ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	27140805

### ETIM

ETIM 10.0	EC000032
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-BS-PG36 - Screw plug



1674545

<https://www.phoenixcontact.com/us/products/1674545>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7c2ea186-890c-44c2-ba72-8041b2de94ab

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)