

SACB-8/ 4P- 5,0PUR-M8 - Housing



1680076

<https://www.phoenixcontact.com/us/products/1680076>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing, connection method: M8 socket, number of slots: 8, number of positions: 4, slot assignment: single, status display: no, Universal; master cable connection: Fixed connection 180°, PUR/PVC, cable length: 5 m

Commercial data

Item number	1680076
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF40
Product key	AF3BCA
GTIN	4017918158262
Weight per piece (including packing)	1.006 kg
Weight per piece (excluding packing)	1.006 kg
Customs tariff number	85444190
Country of origin	CZ

SACB-8/ 4P- 5,0PUR-M8 - Housing



1680076

<https://www.phoenixcontact.com/us/products/1680076>

Technical data

Product properties

Product type	Distributor box
Number of positions	4
Number of slots	8

Electrical properties

Max. operating voltage U_{max}	30 V DC
Nominal voltage U_N	24 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A

Connection data

Conductor connection

Sensor/actuator connection system	M8 socket
Tightening torque slot sensor/actuator cable	0.2 Nm

Signaling

Status display present	no
------------------------	----

Material specifications

Material Housing	PA 6.6
Flammability rating according to UL 94	V0

Cable/line

Cable length	5 m
Cable type	Master cable suitable for flexible cable conduit
Connection method	Fixed connection
Outside diameter	10.9 mm
Conductor cross-section signal conductor	0.34 mm ²
AWG signal line	22
AWG power supply	18
Ambient temperature (operation)	-30 °C ... 70 °C (for fixed installation) -5 °C ... 70 °C (for flexible installation)

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 80 °C

SACB-8/ 4P- 5,0PUR-M8 - Housing

1680076

<https://www.phoenixcontact.com/us/products/1680076>

Drawings




SACB-8/ 4P- 5,0PUR-M8 - Housing

1680076

<https://www.phoenixcontact.com/us/products/1680076>



Schematic diagram



Pin assignment, socket M 8 (female side)

SACB-8/ 4P- 5,0PUR-M8 - Housing



1680076

<https://www.phoenixcontact.com/us/products/1680076>

Classifications

ECLASS

ECLASS-13.0	27440108
ECLASS-15.0	27440108

SACB-8/ 4P- 5,0PUR-M8 - Housing



1680076

<https://www.phoenixcontact.com/us/products/1680076>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com