

VS-08-BU-RJ45/KA - RJ45 jack insert



1689077

<https://www.phoenixcontact.com/us/products/1689077>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 socket insert, modular (Keystone), CAT3, 8-pos., shielded, with cable connection (IDC)

Commercial data

Item number	1689077
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABNMAY
GTIN	4017918876920
Weight per piece (including packing)	16 g
Weight per piece (excluding packing)	16 g
Customs tariff number	85366990
Country of origin	CN

VS-08-BU-RJ45/KA - RJ45 jack insert



1689077

<https://www.phoenixcontact.com/us/products/1689077>

Technical data

Product properties

Product type	Female insert
Number of positions	8

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	125 V
Rated current	1.5 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

Connection data

Connection technology

Connection method	IDC
-------------------	-----

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	Polyester GF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 250
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C


VS-08-BU-RJ45/KA - RJ45 jack insert

1689077

<https://www.phoenixcontact.com/us/products/1689077>

Drawings

Dimensional drawing



RJ45 socket insert, keystone


VS-08-BU-RJ45/KA - RJ45 jack insert

1689077

<https://www.phoenixcontact.com/us/products/1689077>



Schematic diagram



VS-08-BU-RJ45/KA - RJ45 jack insert



1689077

<https://www.phoenixcontact.com/us/products/1689077>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com