

VS-08-KS/GR - RJ45 bending protection sleeve



1689213

<https://www.phoenixcontact.com/us/products/1689213>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 bend protection sleeve, for pin insert VS-08-ST-RJ45, cable cross section up to 6 mm, color: gray

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1689213 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | AB10 |
| Product key | ABNAAZ |
| GTIN | 4017918890582 |
| Weight per piece (including packing) | 1.31 g |
| Weight per piece (excluding packing) | 0.878 g |
| Customs tariff number | 39269097 |
| Country of origin | US |

VS-08-KS/GR - RJ45 bending protection sleeve



1689213

<https://www.phoenixcontact.com/us/products/1689213>

Technical data

Product properties

| | |
|--------------|------------------------|
| Product type | Bend protection sleeve |
|--------------|------------------------|

Dimensions

| | |
|--------|---------|
| Width | 13.7 mm |
| Height | 19.8 mm |
| Length | 9.2 mm |

Material specifications

| | |
|----------------------------------------|------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Housing material | PA |

Cable/line

| | |
|-------------------------|------|
| External cable diameter | 6 mm |
|-------------------------|------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |

VS-08-KS/GR - RJ45 bending protection sleeve



1689213

<https://www.phoenixcontact.com/us/products/1689213>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27440392 |
| ECLASS-13.0 | 27440392 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

VS-08-KS/GR - RJ45 bending protection sleeve



1689213

<https://www.phoenixcontact.com/us/products/1689213>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com