

SACC-SEAL-M12-PW-PPI - Sealing ring

1769794

<https://www.phoenixcontact.com/us/products/1769794>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing ring, Outside diameter: 13 mm, inside diameter: 8.55 mm



Your advantages

- Plug and Produce: quick and reliable connection even in confined spaces
- Easy design-in: countersunk M12 ports for compact device concepts
- Highly future-proof: standardized product range for worldwide availability
- Greater flexibility: one M12 device connection for screw and push-pull connectors
- Time savings of 80% during installation compared to screw connection

Commercial data

Item number	1769794
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	ABQZCC
GTIN	4067923383142
Weight per piece (including packing)	0.34 g
Weight per piece (excluding packing)	0.34 g
Country of origin	DE

SACC-SEAL-M12-PW-PPI - Sealing ring



1769794

<https://www.phoenixcontact.com/us/products/1769794>

Technical data

Product properties

Product type	Seal
--------------	------

Dimensions

Diameter Outside diameter	13 mm
Diameter Inside diameter	8.55 mm

Material specifications

Seal material	FKM
---------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)

SACC-SEAL-M12-PW-PPI - Sealing ring



1769794

<https://www.phoenixcontact.com/us/products/1769794>

Classifications

ECLASS

ECLASS-13.0	27430319
ECLASS-15.0	27430319

ETIM

ETIM 10.0	EC001181
-----------	----------

SACC-SEAL-M12-PW-PPI - Sealing ring



1769794

<https://www.phoenixcontact.com/us/products/1769794>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com