

# HC-D 15-ADP/1 DSUB 25 - Adapter plate



1775266

<https://www.phoenixcontact.com/us/products/1775266>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB adapter plate, for one D-SUB connector, no. of positions 25, housing series HC-D 15...

## Product description

Adapter plate, incl. mounting screws

## Commercial data

Item number	1775266
Packing unit	2 pc
Minimum order quantity	2 pc
Sales key	BF66
Product key	AF7AZD
GTIN	4017918037994
Weight per piece (including packing)	8.14 g
Weight per piece (excluding packing)	8.14 g
Customs tariff number	39269097
Country of origin	DE

# HC-D 15-ADP/1 DSUB 25 - Adapter plate

1775266


<https://www.phoenixcontact.com/us/products/1775266>

## Technical data

### Product properties

Product type	Adapter plate
Type	D15
Number of positions	25
Seal present	yes

### Dimensions

Dimensional drawing	
Width	23 mm
Height	7 mm
Length	57 mm

### Material specifications

Material	PA
Flammability rating according to UL 94	HB

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 100 °C
---------------------------------	-------------------

### Mounting

Assembly note	<p>With mounting screws: 1) Phillips self-tapping screw 2.9 x 6.2/2) M3 x 10 DIN 84</p> <p>Mounting position of the adapter plate in the sleeve housing: <b>T</b> is visible after mounting in the housing. Mounting position of the adapter plate in the panel mounting base/socket housing/coupling housing: <b>A</b> is visible after mounting in the housing. Mounting position of the D-SUB (after mounting in the housing): in front of the mounting panel (front mounting)</p>
---------------	---

# HC-D 15-ADP/1 DSUB 25 - Adapter plate




1775266

<https://www.phoenixcontact.com/us/products/1775266>

## Drawings

Dimensional drawing



See assembly instruction

# HC-D 15-ADP/1 DSUB 25 - Adapter plate



1775266

<https://www.phoenixcontact.com/us/products/1775266>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1775266>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-D 15-ADP/1 DSUB 25 - Adapter plate



1775266

<https://www.phoenixcontact.com/us/products/1775266>

## Classifications

### ECLASS

ECLASS-13.0	27440201
ECLASS-15.0	27440201

### ETIM

ETIM 10.0	EC002309
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-D 15-ADP/1 DSUB 25 - Adapter plate



1775266

<https://www.phoenixcontact.com/us/products/1775266>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.296 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)