


HC-KA-FE - Foot element

1775240

<https://www.phoenixcontact.com/us/products/1775240>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Foot element, for mounting on DIN rail NS 32, DIN rail NS 35/7.5 or DIN rail NS 35/15, can be inserted between basic and side element



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1775240 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF61 |
| Product key | AF7ADZ |
| GTIN | 4017918037970 |
| Weight per piece (including packing) | 3.73 g |
| Weight per piece (excluding packing) | 3.668 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

HC-KA-FE - Foot element



1775240

<https://www.phoenixcontact.com/us/products/1775240>

Technical data

Notes

| | |
|---------|---|
| General | At least two foot elements are necessary per adapter. |
|---------|---|

Product properties

| | |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

Dimensions

| | |
|--------|----------|
| Width | 10 mm |
| Height | 22.85 mm |
| Depth | 42.45 mm |

Material specifications

| | |
|----------|--------|
| Material | PA 6.6 |
|----------|--------|

HC-KA-FE - Foot element



1775240

<https://www.phoenixcontact.com/us/products/1775240>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1775240>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-KA-FE - Foot element



1775240

<https://www.phoenixcontact.com/us/products/1775240>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440192 |
| ECLASS-15.0 | 27440192 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

HC-KA-FE - Foot element



1775240

<https://www.phoenixcontact.com/us/products/1775240>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.026 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com