

HC-B 32-AMQ - Housing

1775693

<https://www.phoenixcontact.com/us/products/1775693>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON panel mounting base B32, with double locking latch, height 30 mm, with flat gasket

Commercial data

Item number	1775693
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAC
GTIN	4017918038267
Weight per piece (including packing)	236.8 g
Weight per piece (excluding packing)	220 g
Customs tariff number	85389099
Country of origin	DE

HC-B 32-AMQ - Housing

1775693

<https://www.phoenixcontact.com/us/products/1775693>



Technical data


Notes

General	For contact inserts HC-B32, DD144, M
---------	--------------------------------------

Product properties

Product type	Housing with locking latch
Housing type	Panel mounting base
Application	Standard
Type	B32
Shielded	no
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	78 mm
Height	31 mm
Length	122 mm

Installation dimensions

Width of the assembly cutout	70 mm
Length of the assembly cutout	84 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Locking latch material	Steel, galvanized

Mechanical properties

Mechanical data

Locking type	Latch
--------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

HC-B 32-AMQ - Housing


1775693

<https://www.phoenixcontact.com/us/products/1775693>




Drawings

Dimensional drawing



Dimensional drawing



Mounting cutout

HC-B 32-AMQ - Housing

1775693

<https://www.phoenixcontact.com/us/products/1775693>



Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

HC-B 32-AMQ - Housing

1775693

<https://www.phoenixcontact.com/us/products/1775693>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com