

# KGS-MSTB 2,5/12 - Cable housing



1783818

<https://www.phoenixcontact.com/us/products/1783818>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable housing, color: green, product range: KGS-MSTB 2,5



## Commercial data

Item number	1783818
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AA08
Product key	AAHZDD
GTIN	4017918041991
Weight per piece (including packing)	20.009 g
Weight per piece (excluding packing)	19.85 g
Customs tariff number	39269097
Country of origin	PL

# KGS-MSTB 2,5/12 - Cable housing



1783818

<https://www.phoenixcontact.com/us/products/1783818>

## Technical data

### Product properties

Product type	Cable housing
Product family	KGS-MSTB 2,5
Number of positions	12
Pitch	0 mm

### Mounting

#### Cable clamp

Tightening torque	0.3 Nm
-------------------	--------

### Material specifications

Color (Housing)	green (RAL 6021)
Insulating material	ABS
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	HB

### Dimensions

Dimensional drawing	
Pitch	-

# KGS-MSTB 2,5/12 - Cable housing


1783818

<https://www.phoenixcontact.com/us/products/1783818>



## Drawings

Dimensional drawing



# KGS-MSTB 2,5/12 - Cable housing



1783818

<https://www.phoenixcontact.com/us/products/1783818>

## Classifications

### ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# KGS-MSTB 2,5/12 - Cable housing



1783818

<https://www.phoenixcontact.com/us/products/1783818>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)