

# KGG-MSTB 2,5/ 4 - Cable housing

1803882

<https://www.phoenixcontact.com/us/products/1803882>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable housing, product range: KGG-MSTB 2,5, width: 19 mm



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1803882       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AA08          |
| Product key                          | AAHZDC        |
| GTIN                                 | 4017918046033 |
| Weight per piece (including packing) | 7.829 g       |
| Weight per piece (excluding packing) | 7.829 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# KGG-MSTB 2,5/ 4 - Cable housing



1803882

<https://www.phoenixcontact.com/us/products/1803882>

## Technical data

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Cable housing |
| Product family      | KGG-MSTB 2,5  |
| Number of positions | 4             |
| Pitch               | 0 mm          |

### Mounting

#### Cable clamp

|                   |        |
|-------------------|--------|
| Tightening torque | 0.2 Nm |
|-------------------|--------|

### Material specifications

|  |     |
|--|-----|
| Insulating material                    | ABS |
| Insulating material group              | I   |
| CTI according to IEC 60112             | 600 |
| Flammability rating according to UL 94 | HB  |

### Dimensions

|        |       |
|--------|-------|
| Width  | 19 mm |
| Height | 37 mm |
| Pitch  | -     |

### Notes

|         |  |
|---------|--|
| General | COMBICON connection plugs can be ordered separately. |
|---------|--|

# KGG-MSTB 2,5/ 4 - Cable housing



1803882

<https://www.phoenixcontact.com/us/products/1803882>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460402 |
| ECLASS-15.0 | 27460402 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# KGG-MSTB 2,5/ 4 - Cable housing



1803882

<https://www.phoenixcontact.com/us/products/1803882>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.059 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)