

STZ 3-PCC 4-7,62 - Strain relief

1840227

<https://www.phoenixcontact.com/us/products/1840227>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 2-position version

Strain relief, for the PCC 4/..-ST and 5-pos. ... 10-pos. MCC 1/..-STZ(F) connector, for snapping into the latching chambers, can be labeled with ZB 6

Commercial data

Item number	1840227
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AA08
Product key	AAHZBJ
GTIN	4017918102296
Weight per piece (including packing)	1.499 g
Weight per piece (excluding packing)	1.452 g
Customs tariff number	85366990
Country of origin	DE

STZ 3-PCC 4-7,62 - Strain relief



1840227

<https://www.phoenixcontact.com/us/products/1840227>

Technical data

Product properties

Product type	Strain relief
Product family	STZ
Number of positions	3
Pitch	7.62 mm

Dimensions

Width	20 mm
Height	3.4 mm
Length	46.8 mm
Pitch	7.62 mm

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

STZ 3-PCC 4-7,62 - Strain relief



1840227

<https://www.phoenixcontact.com/us/products/1840227>

Classifications

ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

ETIM

ETIM 10.0	EC002943
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

STZ 3-PCC 4-7,62 - Strain relief



1840227

<https://www.phoenixcontact.com/us/products/1840227>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.025 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com