

ME MAX 22,5 PLATE YE - Insertion plate



2200591

<https://www.phoenixcontact.com/us/products/2200591>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 19.2 mm, height: 73.6 mm, depth: 1 mm, color: yellow (similar RAL 1018)



Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2200591
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4046356628181
Weight per piece (including packing)	1.74 g
Weight per piece (excluding packing)	0.687 g
Country of origin	DE

ME MAX 22,5 PLATE YE - Insertion plate



2200591

<https://www.phoenixcontact.com/us/products/2200591>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX 22,5..
Ventilation openings present	no

Dimensions

Width	19.2 mm
Height	73.6 mm
Depth	1 mm

Material specifications

Color (Insertion plate)	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

PCB data

Type of PCB mount	Latching
-------------------	----------

Mounting

Mounting type	Slot
---------------	------

ME MAX 22,5 PLATE YE - Insertion plate



2200591

<https://www.phoenixcontact.com/us/products/2200591>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200591>



UL Recognized

Approval ID: E240868

ME MAX 22,5 PLATE YE - Insertion plate



2200591

<https://www.phoenixcontact.com/us/products/2200591>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX 22,5 PLATE YE - Insertion plate



2200591

<https://www.phoenixcontact.com/us/products/2200591>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.016 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com