

# ME B-22,5 MSTBO BUGY VPE50 - Filler plug



2200607

<https://www.phoenixcontact.com/us/products/2200607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points, color: blue gray (similar RAL 7031)

## Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

## Commercial data

Item number	2200607
Packing unit	50 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4046356632232
Weight per piece (including packing)	10.26 g
Weight per piece (excluding packing)	10.26 g
Country of origin	DE

# ME B-22,5 MSTBO BUGY VPE50 - Filler plug



2200607

<https://www.phoenixcontact.com/us/products/2200607>

## Technical data

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Product family	ME B..MSTBO
Ventilation openings present	no

### Material specifications

Color	blue gray (RAL 7031)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching
---------------	----------

# ME B-22,5 MSTBO BUGY VPE50 - Filler plug

2200607

<https://www.phoenixcontact.com/us/products/2200607>



## Classifications

### ECLASS

ECLASS-15.0	27190605
-------------	----------

# ME B-22,5 MSTBO BUGY VPE50 - Filler plug



2200607

<https://www.phoenixcontact.com/us/products/2200607>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)