

UM-ALU 4-72 FRONT 42,5 - Front plate



2200925

<https://www.phoenixcontact.com/us/products/2200925>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Basic profile front plate, width: 71.8 mm, length: 43.8 mm, depth: 2 mm, recommended for UM-ALU 4-..COVER PA.. lateral elements



Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

Commercial data

Item number	2200925
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC14
Product key	ACHDFC
GTIN	4046356720410
Weight per piece (including packing)	18.9 g
Weight per piece (excluding packing)	18 g
Customs tariff number	76061191
Country of origin	DE

UM-ALU 4-72 FRONT 42,5 - Front plate



2200925

<https://www.phoenixcontact.com/us/products/2200925>

Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM-ALU
Product family	UM-ALU 4-72

Dimensions

Width	71.8 mm
Depth	2 mm
Length	43.8 mm

Material specifications

Color (Housing)	aluminum color
Material Housing	Aluminum (anodized)
Surface characteristics	anodized

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 100 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

UM-ALU 4-72 FRONT 42,5 - Front plate

2200925

<https://www.phoenixcontact.com/us/products/2200925>



Drawings

Schematic diagram



UM-ALU 4-72 FRONT 42,5 - Front plate



2200925

<https://www.phoenixcontact.com/us/products/2200925>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-ALU 4-72 FRONT 42,5 - Front plate



2200925

<https://www.phoenixcontact.com/us/products/2200925>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com