

# HBUS 107,6-16P-1S OT BK - Housing half shell



2200976

<https://www.phoenixcontact.com/us/products/2200976>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing for use in distribution boards in accordance with DIN 43880, Upper part shell, color: black (similar RAL 9005)

## Commercial data

Item number	2200976
Packing unit	10 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHBBZ
GTIN	4046356703406
Weight per piece (including packing)	7.44 g
Weight per piece (excluding packing)	7.44 g
Country of origin	DE

# HBUS 107,6-16P-1S OT BK - Housing half shell



2200976

<https://www.phoenixcontact.com/us/products/2200976>

## Technical data

### Product properties

Product type	Housing half shells
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing type	Modular building installation housings
Housing series	BC

### Dimensions

Horizontal pitch	6 Div.
------------------	--------

### Material specifications

Color (Housing half-shell)	black (RAL 9005)
Material Housing half-shell	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# HBUS 107,6-16P-1S OT BK - Housing half shell



2200976

<https://www.phoenixcontact.com/us/products/2200976>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200976>



**UL Recognized**

Approval ID: E240868

# HBUS 107,6-16P-1S OT BK - Housing half shell



2200976

<https://www.phoenixcontact.com/us/products/2200976>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HBUS 107,6-16P-1S OT BK - Housing half shell



2200976

<https://www.phoenixcontact.com/us/products/2200976>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)