

# UM-ALU 4 LID75 PA BK - Lateral element



2200972

<https://www.phoenixcontact.com/us/products/2200972>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, Screw mounting, Side elements (left and right) for profile cover, incl. screws, width: 75.4 mm, length: 9 mm

## Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

## Commercial data

Item number	2200972
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC14
Product key	ACHDFC
GTIN	4046356721141
Weight per piece (including packing)	28.4 g
Weight per piece (excluding packing)	28.4 g
Customs tariff number	39269097
Country of origin	DE

# UM-ALU 4 LID75 PA BK - Lateral element



2200972

<https://www.phoenixcontact.com/us/products/2200972>

## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM-ALU
Product family	UM-ALU
Ventilation openings present	no

### Dimensions

Width	75.4 mm
Length	9 mm

### Material specifications

Color (Side element)	black (RAL 9005)
Material Lateral element	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Screw mounting
Tightening torque / speed	Screw connection with profile cover: 0.8 Nm-1 Nm / rpm- rpm

### Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# UM-ALU 4 LID75 PA BK - Lateral element



2200972

<https://www.phoenixcontact.com/us/products/2200972>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-ALU 4 LID75 PA BK - Lateral element



2200972

<https://www.phoenixcontact.com/us/products/2200972>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)