

# BC 71,6 PLATE KMGY - Insertion plate



2201313

<https://www.phoenixcontact.com/us/products/2201313>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing for use in distribution boards in accordance with DIN 43880, Insertion plate, width: 68.3 mm, height: 41.75 mm, depth: 1.5 mm, color: light gray (similar RAL 7035)



## Your advantages

- Coordinated housing and connection system for faster device development
- Individual online configuration for diverse applications in building automation
- Variety of connection technology
- Can be mounted on the DIN rail or the wall
- With DIN-rail-mountable bus connector and power connector system as an option
- Tool-free mounting
- Available in overall widths from 1 ... 9 width units (17.8 mm ... 161.6 mm)
- Compliant with DIN EN 43880

## Commercial data

Item number	2201313
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHBAZ
GTIN	4046356763035
Weight per piece (including packing)	5.417 g
Weight per piece (excluding packing)	5.417 g
Country of origin	DE

# BC 71,6 PLATE KMGY - Insertion plate



2201313

<https://www.phoenixcontact.com/us/products/2201313>

## Technical data

### Product properties

Product type	Cover
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing type	Modular building installation housings
Housing series	BC
Product family	BC 71,6..
Ventilation openings present	no

### Dimensions

Width	68.3 mm
Height	41.75 mm
Depth	1.5 mm
Horizontal pitch	4 Div.

### Material specifications

Color (Insertion plate)	light gray (RAL 7035)
Material Housing	PC
Flammability rating according to UL 94	V0

# BC 71,6 PLATE KMGY - Insertion plate



2201313

<https://www.phoenixcontact.com/us/products/2201313>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201313>



**UL Recognized**

Approval ID: E240868

# BC 71,6 PLATE KMGY - Insertion plate



2201313

<https://www.phoenixcontact.com/us/products/2201313>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# BC 71,6 PLATE KMGY - Insertion plate



2201313

<https://www.phoenixcontact.com/us/products/2201313>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)