

ME PLC 40 MT S BK - Insertion plate



2201496

<https://www.phoenixcontact.com/us/products/2201496>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Matrix with defined engagement mechanism, for assembly underneath the cover in short design, color: black



Your advantages

- Easy, tool-free mounting

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2201496 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC15 |
| Product key | ACHEAZ |
| GTIN | 4046356838641 |
| Weight per piece (including packing) | 3.69 g |
| Weight per piece (excluding packing) | 3 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

ME PLC 40 MT S BK - Insertion plate



2201496

<https://www.phoenixcontact.com/us/products/2201496>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|------------------------------|------------------|
| Product type | Cover |
| Housing type | DIN rail housing |
| Housing series | ME PLC |
| Product family | ME PLC 40 |
| Ventilation openings present | no |

Dimensions

| | |
|--------|----------|
| Width | 35.27 mm |
| Height | 47.37 mm |
| Depth | 8.7 mm |

Material specifications

| | |
|--|------------------|
| Color (Insertion plate) | black (RAL 9005) |
| Material Housing | PC |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |

Mounting

| | |
|---------------|---------------|
| Mounting type | Clip mounting |
|---------------|---------------|

Packaging specifications

| | |
|----------------------|---------------------|
| Type of packaging | packed in cardboard |
| Outer packaging type | Carton |

ME PLC 40 MT S BK - Insertion plate



2201496

<https://www.phoenixcontact.com/us/products/2201496>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME PLC 40 MT S BK - Insertion plate



2201496

<https://www.phoenixcontact.com/us/products/2201496>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com