

UM108-A/U73-HT 16,0CM - Covering hood

2201610

<https://www.phoenixcontact.com/us/products/2201610>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, Latching, Cover, 73 mm wide, width: 73 mm, length: 160 mm, Note: Max. cover length = PCB length = 19 mm

The figure shows the standard item

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2201610
Packing unit	10 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHDBZ
GTIN	4046356866224
Weight per piece (including packing)	86.6 g
Weight per piece (excluding packing)	80.27 g
Country of origin	DE

UM108-A/U73-HT 16,0CM - Covering hood



2201610

<https://www.phoenixcontact.com/us/products/2201610>

Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

Dimensions

Width	73 mm
Length	160 mm

Material specifications

Color (Covering hood)	transparent
Material	PC
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	Latching
Mounting position	vertical or horizontal

UM108-A/U73-HT 16,0CM - Covering hood



2201610

<https://www.phoenixcontact.com/us/products/2201610>

Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM108-A/U73-HT 16,0CM - Covering hood



2201610

<https://www.phoenixcontact.com/us/products/2201610>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com