

UEGM-SE 5 GY OL EZB402 - Housing half shell



2201983

<https://www.phoenixcontact.com/us/products/2201983>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element for electronic housing UEGM ...

Commercial data

Item number	2201983
Packing unit	10 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHCCB
GTIN	4046356952224
Weight per piece (including packing)	17.22 g
Weight per piece (excluding packing)	17.22 g
Country of origin	DE

UEGM-SE 5 GY OL EZB402 - Housing half shell



2201983

<https://www.phoenixcontact.com/us/products/2201983>

Technical data

Product properties

Product type	Housing half shells
Housing type	Component housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM
Ventilation openings present	yes

Material specifications

Color (Housing)	window gray (RAL 7040)
Material	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

Mounting

Mounting type	Snap in
---------------	---------

UEGM-SE 5 GY OL EZB402 - Housing half shell



2201983

<https://www.phoenixcontact.com/us/products/2201983>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201983>



UL Recognized

Approval ID: E240868

UEGM-SE 5 GY OL EZB402 - Housing half shell



2201983

<https://www.phoenixcontact.com/us/products/2201983>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UEGM-SE 5 GY OL EZB402 - Housing half shell



2201983

<https://www.phoenixcontact.com/us/products/2201983>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com