

# UM-ALU 4-100,5 FRONT 165 AP - Front plate



2202099

<https://www.phoenixcontact.com/us/products/2202099>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, Basic profile front plate, width: 101.8 mm, length: 165 mm, depth: 2 mm, recommended for UM-ALU 4-..COVER AL lateral elements

## Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

## Commercial data

Item number	2202099
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ACHDFZ
GTIN	4046356987660
Weight per piece (including packing)	94.8 g
Weight per piece (excluding packing)	91.5 g
Country of origin	DE

# UM-ALU 4-100,5 FRONT 165 AP - Front plate



2202099

<https://www.phoenixcontact.com/us/products/2202099>

## Technical data

### Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM-ALU
Product family	UM-ALU 4-100,5
Ventilation openings present	no

### Dimensions

Width	101.8 mm
Depth	2 mm
Length	165 mm

### Material specifications

Color (Housing)	aluminum color
Material Housing	Aluminum (anodized)
Surface characteristics	anodized

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

### Mounting

Mounting position	parallel to the DIN rail
-------------------	--------------------------

### Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# UM-ALU 4-100,5 FRONT 165 AP - Front plate

2202099

<https://www.phoenixcontact.com/us/products/2202099>



## Drawings

Schematic diagram



# UM-ALU 4-100,5 FRONT 165 AP - Front plate



2202099

<https://www.phoenixcontact.com/us/products/2202099>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-ALU 4-100,5 FRONT 165 AP - Front plate



2202099

<https://www.phoenixcontact.com/us/products/2202099>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)