

ME MAX/16 2-2 TBUS DEV-PCB - PCB




2202542

<https://www.phoenixcontact.com/us/products/2202542>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Perfboard for the ME-MAX DEV-KIT; for 4-pos. MSTBO header; ideal for manual soldering



Your advantages

- Perfboard for self-assembly (for MSTBO headers)
- Hole matrix dimension: 2.54 mm
- Easy installation

Commercial data

Item number	2202542
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC08
Product key	ACHABD
GTIN	4055626142302
Weight per piece (including packing)	30.5 g
Weight per piece (excluding packing)	29 g
Customs tariff number	85340019
Country of origin	SI

2202542

<https://www.phoenixcontact.com/us/products/2202542>

Technical data

Product properties

Product type	PCB
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME-MAX

Dimensions

Width	95.2 mm
Height	99.2 mm
Depth	1.6 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material	FR 4-21

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	110 °C (depending on power dissipation)
---------------------------------	---

ME MAX/16 2-2 TBUS DEV-PCB - PCB



2202542

<https://www.phoenixcontact.com/us/products/2202542>

Classifications

ECLASS

ECLASS-13.0	27260692
ECLASS-15.0	27260692

ETIM

ETIM 10.0	EC001031
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX/16 2-2 TBUS DEV-PCB - PCB



2202542

<https://www.phoenixcontact.com/us/products/2202542>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com